

CO-Z型 [CO-G型:防振ゴム式]

GMP対応
GMP-compliant
model

Model CO-Z

ケーシング開閉型


Casing opening and closing system

- 外板開閉は、アイボルト式のためボルトの脱着が容易。
- バスケットの取付位置を上にするによりバスケット～フレーム間に広い空間が出来、洗浄後の確認も容易。
- 支持部を防振ゴム式にすることにより、支持部がフレームより低い位置にくる為ケーシング内にコンタミが侵入するのを防ぐ事が出来る。(オプション対応にて標準機は支柱式です)
- バスケット底裏面がフラット形状なため全ての接液・接粉部のスワブ及び目視確認が可能。
- ラビリンスシール式によりケーシング内でのバスケット浸漬洗浄が可能。
- Vベルトによる粉塵防止対策として、電動機下部直結駆動型も対応可能。



※オプション対応機

- Eyebolt system has realized easy attachment / detachment of the bolts for opening and closure of the casing.
- Adequate space is secured between basket and frame by lifting the basket enables the operator to easily perform post-cleaning inspection.
- Replacement of the conventional supporting column with the vibration-proof rubber, the supporting site is located lower than the frame, which can prevent contamination inside the casing. (Also compliant with strut type [Z type].)
- The flat bottom of the basket enables the operator to swab and visually inspect every area having contact with Liquid/Solid.
- The labyrinth seal system enables the operator to perform intra-casing immerse cleaning of the basket.
- The model with the lower motor drive incorporating a V-belt can also be used for dust prevention.



仕様 (Specification)

機械型式 Model	バスケット寸法 Basket size	最大容量 Capacity (ℓ)	回転数 Revolutions per minute (rpm)	遠心効果 Centrifugal effects (G)	モータ Motor (kW)	概算質量 Approximate weight (kg)	概略寸法 (mm) Approximate size			
	直径×深さ (mm) Diameter × Depth						A	B	C	D
CO-20-Z	485× 275	25	1800	880	2.2	630	960	1420	880	1520
CO-24-Z	610× 275	40	1600	870	2.2	730	1120	1580	940	1650
CO-30-Z	760× 330	60	1250	660	3.7～5.5	1000	1300	1870	1120	1980
CO-36-Z	915× 360	95	1100	620	5.5～7.5	1400	1560	2130	1220	2350
CO-42-Z	1070×410	150	950	540	7.5～11	1800	1750	2280	1350	2700

※ウェットケーキの見掛け比重が大きい場合は、別途ご相談ください。* Consult with TANABE individually if apparent specific gravity of the wet cake is heavy.
※お引き合い時、詳細資料を提出いたします。* Detailed data will be supplied at the time of inquiry.